

CT120800L00

by Burndy
Catalog ID: CT120800L00

Nylon cable Tie, 120 lbs.

- Standard Cable Tie
- Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool



Product Details

General

| | |
|---------------------------------------|------------------------------------|
| Application | For connecting cable to ground rod |
| Color | UV Black (Mil. Spec.) |
| Material | Nylon 6/6 |
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |
| Rating - Minimum Tensile Strength lbs | 120 |
| Sub Brand | UNIRAP |
| Tool Type | Standard |
| Trade Name | UNIRAP™ |
| Type | STANDARD |
| UPC | 781810661086 |

Dimensions

| | |
|--------------------------------------|----------|
| Dimension - Bundle Diameter Max inch | 8 |
| Dimension - L Length Overall mm | 724 mm |
| Dimension - Length Overall inch | 28.51 in |
| Dimension - Width inch | 0.30 in |
| Dimension - Width mm | 7.6 mm |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | Yes |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|--------|
| Carton Quantity | 500 EA |
| Minimum Pack Quantity | 50 |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)