



CT1751100Q0

by Burndy
Catalog ID: CT1751100Q0

UV Black Nylon 6/6 Cable Tie, 11" Max. Bundle Dia, 175 Lbs, 36" Long, 0.35" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool

Product Details

General

Application	For Outdoor Applications
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334133

Dimensions

Dimension - Bundle Diameter Max inch	11
Dimension - L Length Overall mm	927 mm
Dimension - Length Overall inch	36.50 in
Dimension - Width inch	0.34 in
Dimension - Width mm	8.6 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Military Spec Number	MS3367-13-0
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)