

## CT250600QO



by Burndy  
Catalog ID: CT250600QO

UV Black Nylon 6/6 Cable Tie, 6" Max. Bundle Dia, 250 Lbs, 23" Long, 0.50" Wide.

- Standard Cable Tie

Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT2, MK9 Tool

## Product Details

### General

Application	For Outdoor Applications
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334645

### Dimensions

Dimension - Bundle Diameter Max inch	6.10 in
Dimension - L Length Overall mm	579 mm
Dimension - Length Overall inch	22.80 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

### Certifications and Compliance

Certification - 94VO Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)