



CT250600RQ0

by Burndy
Catalog ID: CT250600RQ0

Nylon 6/6 Standard Releasable Cable Tie, UV Black, 250 Lbs Min Ten Strgth, 23.00" L, 0.50" W.

- Releasable

Features: Perfect For Prototype Construction, Releasable Cable Ties Are Ideal For Temporary Installations, Releasable Ties Are Also Good For Applications Where Service Requires Adding Or Subtracting Wires From An Existing Wire Bundle

Product Details

General

Application	For Use Where Service Requires Adding Or Subtracting Wires From An Existing Wire Bundle
Color	Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	250
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Heavy Duty Releasable
UPC	781810334850

Dimensions

Dimension - Bundle Diameter Max inch	6
Dimension - L Length Overall mm	559 mm
Dimension - Length Overall inch	22 in
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)