

CT40200C0

by Burndy
Catalog ID: CT40200C0

UV Black Nylon 6/6 Cable Tie, 2" Max. Bundle Dia, 40 Lbs, 8.50" Long, 0.15" Wide.

- Standard Cable Tie
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Installation Tool: TWT1, MK7 Tool



Product Details

General

Application	For Outdoor Applications
Color	UV Black
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Intermediate
Trade Name	UNIRAP™
Type	Intermediate
UPC	781810332382

Dimensions

Dimension - Bundle Diameter Max inch	2
Dimension - L Length Overall mm	225 mm
Dimension - Length Overall inch	8.87 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)