



# CT40200M00

by Burndy  
Catalog ID: CT40200M00

Nylon cable ties, Tensile strength-40 Lbs, Color- UV Black, 08.87"L,  
0.14"W, 02.37" Bundle Dia.

- Standard Cable Tie

## Product Details

### General

|                                       |              |
|---------------------------------------|--------------|
| Color                                 | Black        |
| Material                              | Nylon 6/6    |
| Operating Temperature Celcius Max     | 85 °C        |
| Operating Temperature Celcius Min     | -40 °C       |
| Rating - Minimum Tensile Strength lbs | 40           |
| UPC                                   | 781810332337 |

### Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 2.37 in |
| Dimension - L Length Overall mm      | 225 mm  |
| Dimension - Length Overall inch      | 8.87 in |
| Dimension - Width inch               | 0.14 in |
| Dimension - Width mm                 | 4 mm    |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - 94V0 Rated         | N   |
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - UV Rated           | Yes |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |

### Logistics

|                       |         |
|-----------------------|---------|
| Carton Quantity       | 5000 EA |
| Minimum Pack Quantity | 1000    |
| Packaging Type        | Bag     |

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)