



## CT40300SSBCO

by Burndy

Catalog ID: CT40300SSBCO

Nylon Stainless Steel BARB Cable Ties, 11.18 IN L, .14 IN W, Tensile Strength: 40 Lbs,Max bundle dia:3.15".

- Stainless Steel Barb Tie

Nylon 6/6 Standard, Self-locking stainless steel barb,Maximum strength and adjustability for versatility

## Product Details

### General

Application	For use with self-locking stainless steel barb
Color	Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564554

### Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	284 mm
Dimension - Length Overall inch	11.18 in
Dimension - Width inch	0.14 in
Dimension - Width mm	4 mm

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	8000 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)