



## CT50175MH10C0

by Burndy  
Catalog ID: CT50175MH10C0

UV Black Nylon 6/6 Mounting Hole Cable Tie, # 10 Stud, 1.75" Max. Bundle Dia, 50 Lbs, 8.50" Long, 0.18" Wide.

- Mounting Hole
- Features: Cable Ties for General Use Available in Black or Natural, One piece injection molded, Stud Size: #10 (M5), Installation Tool: MK7 Tool

### Product Details

#### General

|                                       |                  |
|---------------------------------------|------------------|
| Application                           | For Screw Mount  |
| Color                                 | Black            |
| Material                              | Nylon 6/6        |
| Mounting Method                       | Screw            |
| Operating Temperature Celcius Max     | 85 °C            |
| Operating Temperature Celcius Min     | -40 °C           |
| Rating - Minimum Tensile Strength lbs | 50               |
| Sub Brand                             | UNIRAP,CABLE TIE |
| Trade Name                            | UNIRAP™          |
| Type                                  | Standard         |
| UPC                                   | 781810335260     |

#### Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.75 in |
| Dimension - L Length Overall mm      | 203 mm  |
| Dimension - Length Overall inch      | 8.00 in |
| Dimension - Screw Size inch          | #10     |
| Dimension - Width inch               | 0.17 in |
| Dimension - Width mm                 | 4 mm    |

#### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - 94V0 Rated         | N   |
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - UV Rated           | Yes |
| Certification - cULus              | Yes |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |

#### Logistics

|                 |         |
|-----------------|---------|
| Carton Quantity | 5000 EA |
|-----------------|---------|

Minimum Pack Quantity

100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)