



CT50300SSBC0

by Burndy
Catalog ID: CT50300SSBC0

Nylon Stainless Steel BARB Cable Ties, 11.61 IN L, .19 IN W, Tensile Strength: 50 Lbs,Material:Nylon 6/6.

- Stainless Steel Barb Tie
- Features: Cable Ties for General Use Available in Black, Material-nylon 6/6

Product Details

General

Application	For use with self-locking stainless steel barb
Color	Black
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810564677

Dimensions

Dimension - Bundle Diameter Max inch	3.19
Dimension - L Length Overall mm	295 mm
Dimension - Length Overall inch	11.61 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	6000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)