



## CT50425SSBC

by Burndy

Catalog ID: CT50425SSBC

Nylon Stainless Steel BARB Cable Ties, 14.96 IN L, .19 IN W, Tensile Strength: 50 Lbs, Color: Natural.

- Stainless Steel Barb Tie

Features: Cable Ties for General Use Available in Natural Color, Material-nylon 6/6

## Product Details

### General

Application	For use with self-locking stainless steel barb
Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	50
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810564714

### Dimensions

Dimension - Bundle Diameter Max inch	4.21
Dimension - L Length Overall mm	380 mm
Dimension - Length Overall inch	14.96 in
Dimension - Width inch	0.19 in
Dimension - Width mm	5 mm

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	5000 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)