



CTB075RA4C

by Burndy
Catalog ID: CTB075RA4C

Rubber Adhesive Cable Tie Mounting Base, 0.14" Max. Tie Slot Width.

- Cable Tie Base
- Features: Rubber Adhesive mounting

Product Details

General

Application	For used in conjunction with cable ties to stabilize and secure wire bundles
Color	Natural
Material	Nylon 6/6
Mounting Method	Rubber adhesive or #4 screw
Operating Temperature Celcius Max	70 °C
Operating Temperature Celcius Min	0 °C
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	Cable Tie Bases
UPC	781810335802

Dimensions

Dimension - B Length inch	0.74 in
Dimension - Width inch	0.74 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)