



## CTSS100200FC304C

by Burndy  
Catalog ID: CTSS100200FC304C

Fully coated stainless steel cable ties 304 grade, Tensile strength: 160 Lb, 7.87" L, 0.18" W, 1.97" Bundle Dia.

- Stainless Steel Cable Tie - Fully Coated

### Product Details

#### General

|                                       |                           |
|---------------------------------------|---------------------------|
| Material                              | Stainless Steel, Type 304 |
| Operating Temperature Celcius Max     | 115 °C                    |
| Operating Temperature Celcius Min     | -40 °C                    |
| Operating Temperature Range Celcius   | -40 - 115                 |
| Rating - Minimum Tensile Strength lbs | 160                       |
| Trade Name                            | UNIRAP™                   |
| UPC                                   | 781810646977              |

#### Dimensions

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 1.97    |
| Dimension - L Length Overall mm      | 200 mm  |
| Dimension - Length Overall inch      | 7.87 in |
| Dimension - Width inch               | 0.18 in |
| Dimension - Width mm                 | 4.6 mm  |

#### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

#### Logistics

|                       |         |
|-----------------------|---------|
| Carton Quantity       | 6500 EA |
| Minimum Pack Quantity | 100     |

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)