



CUW34E

by Burndy
Catalog ID: CUW34E

Prop 65 Notice

Deadend Clamp, 4/0 Str. - 500, 7-3/8 in L, 4 in Width, Bright Dipped.

Features: High Strength, Two-Bolt, Cast Copper Alloy Strain Clamp With Single Saddle Designed For Short Span Distribution And Strain Bus Application, Galvanized Steel Clevis Pin, And U-Bolts, Length: 7-3/8 IN, Width: 4 IN, Height: 3 IN

Product Details

General

Application	For Short Span Distribution And Strain Bus Application
Connector Type	Deadend
Material	Copper Alloy
Material - Hardware	Galvanized Steel
Plated	Y
Plating Type	Bright Dipped
Sub Brand	DEADEND CLAMP
Type	CUW-E
UPC	781810091708

Dimensions

Dimension - B Length fraction	2-81/89 in
Dimension - B Length inch	2.91 in
Dimension - Height fraction	3
Dimension - Height inch	3 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.38 in
Dimension - Width fraction	3-81/89 in
Dimension - Width inch	3.91 in
Dimension - Width mm	99 mm

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)