



CY4/OL22G5TN

by Burndy
Catalog ID: CY4/OL22G5TN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810668979
UPC 12 Digit	7818106689799

Dimensions

Dimension - L Length Overall mm	559 mm
Dimension - Length Overall inch	22 in
Weight	0.288 lb

Electrical Ratings

Amperage Rating	335 A
-----------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	40
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)