



EPP10

by Burndy
Catalog ID: EPP10

Prop 65 Notice

Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts, 10000 psi, 115V AC/60Hz.

- Lightweight
- Small size
- Factory set relief valve
- 100,000 (+) life cycles
- Sealed electric pendant switch

Features: Lightweight, Small Size, Factory Set Relief Valve, 100000 (+) Life Cycles, Sealed Electric Pendant Switch, High Quality Crimps Are Achieved With Built In, Factory Set Pressure Release Valve And Audible Recycling Of Pump To Signal Completion Of Crimp Cycle, Easy To Lift, Carry And Transport Tool Around Job Site With Lightweight Body And Handle, Convenient 115 VAC Electric Powered Motor, Durable Remote Pendant Switch, Easy Operation Controlled With Pendant Switch, Or Manual Switch, Saves Time With Quick Disconnect Hydraulic Fitting, Long Durable Life Expectancy With Lightweight Cast Aluminum Reservoir Body, 5-Year Limited Warranty, The Lightweight And Durable EPP10 Electric/Hydraulic Pump Is For Use With All BURNDY HYPRESS Remote Heads And Cutters Requiring 10000 PSI Operating Pressure, Both The EPP10 And The EPP6 Are Equipped With A Built-In, Factory Set Pressure Relief Valve, An Audible Pop And Recycling Of The Pump And Relaxing Of The Hose, Signals Completion Of The Crimping/Cutting Cycle, Both Pumps Are Supplied With A Durable Hand-Held Electric Pendant Switch, For Remote Operation Of The Unit, And Have A Manual Selection Switch Mounted For Operation Of The Unit At The Pump, The Operator Can Select Which Method Is Best Suited For The Application, An Optional Carry/Shipping Case Can Be Ordered, All EPP Series Pumps Have Been Life Cycle Tested To Over 100000 Cycles Without Failure, And Are Warranted To Be Free Of Defects In Materials And Workmanship For Five (5) Years When Properly Maintained And Operated, Current Draw (maximum): 12.5 AMP, Reservoir Volume: 2 QT, Weight: 30 LB, Base: 6 X 8 IN, Accessories: EPPCASE-1 Steel Carrying Case With Handle And Locking Latch, Replacement Fluid: Alfluid5 year limited warranty

Product Details

General

| | |
|--------------|---|
| Application | For Y34BH, Y35BH, Y35BH-4, Y39BH, Y45, Y46, Y46C, Y60BHU, 750BH, Y750BH-2, Y644MBH, RHCC Series Cutters |
| Power Source | 1/2 HP 115 V AC/60 Cycle |
| Sub Brand | HYDRAULIC PUMP |
| Tool Type | Electric Hydraulic Pump |
| Type | Pumps |
| UPC | 781810033456 |
| UPC 12 Digit | 7818100334566 |

Dimensions

| | |
|--------|-------|
| Height | 16 in |
| Length | 8 in |
| Weight | 30 lb |
| Width | 6 in |

Electrical Ratings

| | |
|------------------|-------|
| Current Draw Max | 12.5A |
|------------------|-------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)