



ES25A6R

by Burndy Catalog ID: ES25A6R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:2 S.B. 200% |8 S.B. 200% AL & CU:1/0 STR-1/0 STR|6 STR.-6 STR. COLOR/COULEUR: A-YELLOW, B-BLUE

Product Details

General		
Die Index	BG	
Insulation	Y	
Insulation Type	Nylon	
Material	Aluminum	
Plated	Y	
Plating Type	Tin - Hot Dipped	
Prefilled Oxide Inhibitor	Y	
Trade Name	INSULINK™	
Туре	Insulated Service Entrance Connectors	
UPC	781810420454	
UPC 12 Digit	7818104204544	

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	100	
-		

BURNDY Headquarters 47 East Industrial Park Drive Manchester, New Hampshire 03109 Customer Service Hours: 8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)