



## ES25R2RBOX

by Burndy  
Catalog ID: ES25R2RBOX

Prop 65 Notice

ACSR: 1/0, #1 #2 AL/CU: 1/0, #1(19 STR) AL/CU #2, #1 INDEX: BG, 5/8"  
A(YELLOW) B(RED)

## Product Details

### General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191712
UPC 12 Digit	7818101917122

### Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

### Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - ACSR Str Size B	2 AWG
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	2 STR, 1 STR
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	2 STR, 1 STR

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)