



ES25R2WBOX

by Burndy
Catalog ID: ES25R2WBOX

Prop 65 Notice

ACCOM: A: 1/0,1 ACSR, 1/0 STR, 1-19 STR ALUM & CU B: 4 ACSR, 3,4 STR,
2 SOL INDEX: BG OR 5/8" COLOR: A: YELLOW B: ORANGE

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Type	Insulated Service Entrance Connectors
UPC	781810191729
UPC 12 Digit	7818101917299

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - ACSR Str Size B	4 AWG
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	3 STR, 4STR,2 SOL
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	3 STR, 4STR,2 SOL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)