



## ES25R4WBOX

by Burndy  
Catalog ID: ES25R4WBOX

Prop 65 Notice

ACSR: 1/0, #1 #6 AL/CU: 1/0, #1(19 STR) #5, #6 STR AL/CU #4 SOL  
INDEX: BG, 5/8 A(YELLOW) B(BLUE)

## Product Details

### General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191736
UPC 12 Digit	7818101917366

### Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

### Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - ACSR Str Size B	6 AWG
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	5 STR, 6 STR, 4 SOL
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	5 STR, 6 STR, 4 SOL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	96
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)