



ES25R6WBOX

by Burndy
Catalog ID: ES25R6WBOX

Prop 65 Notice

ACSR: 1-1/0 8 STR AL/CU: 1/0 AL/CU 6 SOL INDEX: BG, 5/8" A(YELLOW)
B(GREEN)

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810191743
UPC 12 Digit	7818101917433

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	1/0 STR, 1 STR
Conductor - AL Str Size A	1/0 STR
Conductor - AL Str Size B	8 STR, 6 SOL
Conductor - Copper Str Size A	1/0 STR
Conductor - Copper Str Size B	8 STR, 6 SOL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)