



## ES4R6R

by Burndy  
Catalog ID: ES4R6R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:6 S.B. 200% |8 S.B. 200% AL & CU:4 SOL-4 STR.|6 SOL-6 STR. COLOR/COULEUR: A-ORANGE, B-BLUE

## Product Details

### General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420409
UPC 12 Digit	7818104204099

### Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

### Conductor Related

Conductor - ACSR Str Size A	4 AWG
Conductor - ACSR Str Size B	6 AWG
Conductor - AL Str Size A	4 AWG
Conductor - AL Str Size B	6 AWG
Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	6 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

**Logistics**

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)