



ES4W4W

by Burndy Catalog ID: ES4W4W

Prop 65 Notice

Insulated AL service entrance compression sleeve for combinations of insulated CU, AL and ACSR conductors, Color Code: Blue (Side A), Blue (Side B).

Features: Pre-Insulated Service Entrance Compression Connector Installed With OH25, OUR840 And MD6 HYTOOL As Well As Y35 And Y750 HYPRESS Tools, Polyethylene Caps Prevent Dirt From Accumulating In Barrel, Grip Cable For Easy Two-Hand Installation, And Seal Out Moisture, Aluminum Connector Is Anchored To Jacket, Assuring The Connector Is Under The Die When Crimping, Nylon Jacket Insulates Connector Electrically And Protects Against Water And Weather, Superior Color Coding, Pre-Filled With PENETROX Joint Compound, Tools, Die Set Catalog Number, And (number Of Crimps): HYTOOL: OH25 Tool, (1), MD6, MD7 Tool, (3), MD6, MD7 Tool, W-BG Die, (1), OUR840 Tool, X-NBG Die, (1), HYPRESS: Y35 Tool, U-BG Die, (1), Y750 Tool, Die Index: BG Element A, Conductor Type: Side A And Side B: ACSR, Aluminum, Copper, Color Code: Blue (Side A And B)

Product Details

General

Application	For Insulated Combinations Of Copper, Aluminum, ACSR Compressed Conductors And In Overhead Distribution
Color Code - Side A	Blue
Color Code - Side B	Blue
Die Index	BG or 5/8
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Sub Brand	INSULINK
Trade Name	INSULINK™
Туре	Insulated Service Entrance Connectors
UPC	781810142455
UPC 12 Digit	7818101424555

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	6 (6/1) Turkey AWG

Conductor - ACSR Str Size B	6 (6/1) Turkey AWG
Conductor - AL Str Size A	6 AWG;5 AWG
Conductor - AL Str Size A Range	6 AWG-5 AWG
Conductor - AL Str Size B	6 AWG;5 AWG
Conductor - AL Str Size B Range	6 AWG-5 AWG
Conductor - Copper Solid Size A	4 AWG
Conductor - Copper Solid Size A Range	4 AWG
Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Solid Size B Range	4 AWG
Conductor - Copper Str Size A	6 AWG;5 AWG
Conductor - Copper Str Size A Range	6 AWG-5 AWG
Conductor - Copper Str Size B	6 AWG;5 AWG
Conductor - Copper Str Size B Range	6 AWG-5 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)