



# FD67C6

by Burndy  
Catalog ID: FD67C6

Prop 65 Notice

Stud connector, 4 Holes, 1075 AMP Nominal, 1 1/2"-12 Stud, 9/16"pad holes,  
1-3/4" Spacing, 6.23"length, 3"width, Stud to Flat Bar

## Product Details

### General

|                     |                           |
|---------------------|---------------------------|
| Application         | Substation                |
| Connector Type      | Stud Connector            |
| Material            | Copper Alloy              |
| Material - Hardware | DURIUM™ Silicon Bronze    |
| Plated              | N                         |
| Plating Type        | Unplated                  |
| Type                | Studs Busbar Tap          |
| UPC                 | 662620318318 781810003596 |
| UPC 12 Digit        | 7818100035966             |

### Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Dimension - B Length fraction     | 2-9/50 in |
| Dimension - B Length inch         | 2.18 in   |
| Dimension - Bolt Size fraction    | 1/2       |
| Dimension - D inch                | 3.00 in   |
| Dimension - Length Overall inch   | 6.23 in   |
| Dimension - Pad Width inch        | 3.00 in   |
| Dimension - Pin Diameter fraction | 1-1/2 in  |
| Dimension - Pin Diameter inch     | 1.500 in  |

### Electrical Ratings

|                 |        |
|-----------------|--------|
| Amperage Rating | 1075 A |
| Rating - KVA    | 230 kV |

### Conductor Related

|                                    |             |
|------------------------------------|-------------|
| Conductor - Connection Combination | Stud to Pad |
| Conductor - Copper Str Run         | 4/0         |

### Certifications and Compliance

|                     |    |
|---------------------|----|
| Certification - ETL | No |
|---------------------|----|

### Logistics

|                 |       |
|-----------------|-------|
| Carton Quantity | 10 EA |
|-----------------|-------|

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)