



## GAR114C

by Burndy  
Catalog ID: GAR114C

Prop 65 Notice

Ground Clamp-Cable to Rebar, 8 Sol. - 4 Str., Bright Dipped.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Tube (ips) Size: 1/4 IN, Ground Rod Size: 1/2 IN, Installation Torque: 240 IN-LB, Height: 2-1/2 IN, Width: 1-7/8 IN

## Product Details

### General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Installation Torque Recommended Run in-lb	240 Lb in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	271
UPC	781810231005
UPC 12 Digit	7818102310055

### Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height fraction	2-1/2 in
Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Outside Diameter inch	0.54 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

### Conductor Related

Conductor - Copper Solid Size	8 AWG
Conductor - Copper Solid Size Range	8 AWG-3 AWG
Conductor - Copper Str Size	4 AWG

Conductor - Copper Str Size Range	9 AWG-4 AWG
Conductor - Copper Tube Std Size	1/4 IPS IPS
Conductor - Copper Tube Std Size Range	1/4 IPS IPS
Conductor - Pipe or Round Tube Size Range	1/4 in
Conductor - Rod Size	.5 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)