



GAR1426W

by Burndy
Catalog ID: GAR1426W

Prop 65 Notice

To Rod or Pipe with the Same Connector.

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin Plated bodies and electro tin plated hardware
U Bolt Type	249
UPC	781810167861
UPC 12 Digit	7818101678611

Dimensions

Dimension - B Length inch	1.50 in
Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	1.05 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	1/2;3/4
Conductor - Copper Tube Std Size Range	1/2-3/4
Conductor - Pipe or Round Tube Size Range	1/2-3/4 in
Conductor - Rebar Size	7;8
Conductor - Rebar Size Range	7-8
Conductor - Rod Size	1 in
Conductor - Rod Size Range	7/8-1

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)