



# **GAR1529**

by Burndy Catalog ID: GAR1529

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 1" Pipe, 1-1/8"-1-1/4" Rod, #9-#10 Rebar, Bright Dipped.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Height: 3-3/8 IN, Tube (ips) Size: 1 IN, Ground Rod Size: 1-1/8 - 1-1/4 IN, Rebar Size: #9 (1-1/8 IN) - #10 (1-1/4 IN), Installation Torque: 240 IN-LB, Width: 2-5/8 IN

# **Product Details**

#### General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Installation Torque Recommended Run in-lb	240 Lb in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Туре	GAR
U Bolt Type	244
UPC	781810232804
UPC 12 Digit	7818102328044

#### **Dimensions**

Dimension - B Length inch	1.75 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

### Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	250 Kcmil

Conductor - Copper Str Size Range	1/0 -250 kcmil
Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Copper Tube Std Size Range	1 IPS IPS
Conductor - Pipe or Round Tube Size Range	1 in
Conductor - Rebar Size	9; 8
Conductor - Rebar Size Range	8 -9
Conductor - Rod Size	1.120-1.31 in
Conductor - Rod Size Range	1 1/8 in-1 1/4 in
Conductor Type	<ul><li>CU C Solid-Size</li><li>CU C Str-Size</li><li>CU Tube Std-Size</li><li>Rod-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

### For further technical assistance, please contact us

BURNDY Headquarters 47 East Industrial Park Drive Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)