



GAR1734

by Burndy
Catalog ID: GAR1734

Prop 65 Notice

To Rod or Pipe with the Same Connector.

Product Details

General

Installation Torque Recommended Run in-lb	480 Lb in
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
U Bolt Type	302
UPC	781810234600
UPC 12 Digit	7818102346000

Dimensions

Dimension - B Length inch	2.50 in
Dimension - Height fraction	4-5/8 in
Dimension - Height inch	4.63 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	1.90 in
Dimension - Width fraction	2-5/8 in
Dimension - Width inch	3.62 in
Dimension - Width mm	92 mm

Conductor Related

Conductor - Copper Solid Size	300 Kcmil
Conductor - Copper Str Size	500 Kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil
Conductor - Copper Tube Std Size	1 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	1 1/2 IPS IPS
Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor - Rod Size	1.620-1.90 in
Conductor - Rod Size Range	1 5/8 in-1 7/8 in

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)