



## GAR1934

by Burndy  
Catalog ID: GAR1934

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 300 - 500 kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe, Bright Dipped.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 2-1/2 - 2-7/8 IN, Tube (ips) Size: 2-1/2 IN, Width: 4-5/8 IN, Installation Torque: 480 IN-LB, Height: 5-5/8 IN

## Product Details

### General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Installation Torque Recommended Run in-lb	480 Lb-in
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	347
UPC	781810236109
UPC 12 Digit	7818102361099

### Dimensions

Dimension - B Length inch	3.38 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	2.88 in
Dimension - Width fraction	4-5/8 in
Dimension - Width inch	4.36 in
Dimension - Width mm	111 mm

### Conductor Related

Conductor - Copper Solid Size	300 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	300 kcmil-500 kcmil

Conductor - Copper Tube Std Size	2 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor - Pipe or Round Tube Size Range	2-1/2 in
Conductor - Rod Size	2.5 in-2.88 in
Conductor - Rod Size Range	2 1/2 in-2 7/8 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)