



## GAR214CW

by Burndy  
Catalog ID: GAR214CW

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG -4 AWG, 3-1/2" Pipe, 3-1/2"-4" Rod, Tin Hot Dipped

## Product Details

### General

Installation Torque Recommended in-lb	240 LBS/in
Plating Type	Tin - Hot Dipped
U Bolt Type	264
UPC	781810051511

### Dimensions

Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Width fraction	5-3/8 in
Dimension - Width inch	5.31 in
Dimension - Width mm	135 mm

### Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4;3
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	9;8;7;6;5;4
Conductor - Copper Str Size Range	9-4
Conductor - Copper Tube Std Size	3 1/2;4
Conductor - Copper Tube Std Size Range	3 1/2-4
Conductor - Pipe or Round Tube Size	3 1/2 in
Conductor - Rod Size	3.5 - 4.0 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)