



GAR244C

by Burndy
Catalog ID: GAR244C

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG (Sol) - 4 AWG (STR), 5" Pipe, Bright Dipped.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
U Bolt Type	122
UPC	781810001479
UPC 12 Digit	7818100014799

Dimensions

Dimension - B Length inch	4.50 in
Dimension - Height fraction	7-3/4 in
Dimension - Height inch	7.75 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	5.56 in
Dimension - Width fraction	6-7/8 in
Dimension - Width inch	6.88 in
Dimension - Width mm	175 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	9 AWG-4 AWG
Conductor - Copper Tube Std Size	5 IPS IPS
Conductor - Copper Tube Std Size Range	5 IPS IPS
Conductor - Pipe or Round Tube Size	5 in
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)