



## GAR8626

by Burndy  
Catalog ID: GAR8626

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)- 2/0 AWG (Str), 6" Pipe, Bright Dipped

## Product Details

### General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
UPC	781810079089
UPC 12 Digit	7818100790899

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length BB inch	1.69 in
Dimension - Length Overall inch	1.69 in
Dimension - Outside Diameter inch	6.63 in
Dimension - Width inch	8.38 in
Dimension - Width mm	213 mm

### Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Solid Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size Range	5-2/0
Conductor - Copper Tube Std Size	6
Conductor - Copper Tube Std Size Range	6
Conductor - Pipe or Round Tube Size	6 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	4
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)