

GB26T4GSTN

by Burndy
Catalog ID: GB26T4GSTN

Mechanical Grounding Connector, Cable to 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), Hardware: GALVANIZED STEEL, Tin Plated



Product Details

General

Installation Torque Recommended in-lb	240 lb-in
Plating Type	Tin Plated
UPC	621945461635

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Height inch	2.18 in
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-5/9 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
-------------------------------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)