



## GBM28CG2

by Burndy  
Catalog ID: GBM28CG2

Prop 65 Notice

Cable Tray Ground Clamp CU CABLE: #1 AWG (STR) - 4/0 AWG (STR)  
1/4" STUD TORQUE: 35 LB IN Tin Plated

## Product Details

### General

Installation Torque Recommended in-lb	35 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Tin - Electro Plated
UPC	781810424315
UPC 12 Digit	7818104243155

### Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height inch	0.76 in
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.38 in
Dimension - Width fraction	1-2/5 in
Dimension - Width inch	1.41 in
Dimension - Width mm	36 mm

### Conductor Related

Conductor - Copper Solid Size Range	#1 AWG-4/0 AWG
Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1 AWG-4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)