



GC30G3

by Burndy
Catalog ID: GC30G3

Prop 65 Notice

Ground Connector, CU CABLE: #4 AWG - 300 KCMIL

Product Details

General

Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	N
Plating Type	Unplated
UPC	781810117460
UPC 12 Digit	7818101174600

Dimensions

Dimension - Height inch	3.27 in
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.41 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

Conductor Related

Conductor - Copper Solid Size Range	#4 AWG - 300 KCMIL
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	4 AWG-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)