



## GCL30T4

by Burndy  
Catalog ID: GCL30T4

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to 1/4" - 1/2" Thick Bar, #4 AWG - 300 KCMIL, 1/2" Stud

## Product Details

### General

|                                       |                        |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 480 lb-in              |
| Material                              | Copper Alloy           |
| Material - Hardware                   | DURIUM™ Silicon Bronze |
| Physical Attribute - Screw Type       | Hexagonal Bolt         |
| Plated                                | N                      |
| Plating Type                          | Unplated               |
| UPC                                   | 781810122303           |
| UPC 12 Digit                          | 7818101223033          |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Bus Thickness inch  | 0.25 in |
| Dimension - L Length Overall mm | 56 mm   |
| Dimension - Length Overall inch | 2.21 in |
| Dimension - Stud Size inch      | 33/64   |
| Dimension - Width inch          | 1.50 in |
| Dimension - Width mm            | 38 mm   |

### Conductor Related

|                                     |  |
|-------------------------------------|--|
| Conductor - Copper Solid Size       | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG                        |
| Conductor - Copper Solid Size Range | 4 AWG - 300 KCMIL  |
| Conductor - Copper Str Size         | 5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil |
| Conductor - Copper Str Size Range   | 5 AWG-300 kcmil  |

### Certifications and Compliance

|   |     |
|---|-----|
| Certification - UL Listed Direct Burial | Yes |
| Standards - RoHS Compliance Status      | CM  |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)