



GD1726TN

by Burndy
Catalog ID: GD1726TN

ACCOMMODATES: 4SQL - 2/0STR PIPE SIZE: 1-1/2" IPS ROD SIZE: 1-5/8"
to 1-7/8" TIN PLATED DIRECT BURIAL

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Electro Plated
U Bolt Type	268
UPC	781810343456
UPC 12 Digit	7818103434566

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	4;3;2;1;1/0;2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size	4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Str Size Range	4-2/0
Conductor - Copper Tube Std Size	1-5/8;1-3/4;1-7/8
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)