



GD174C

by Burndy
Catalog ID: GD174C

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 8 AWG (Sol) - 4 AWG (Str), 1-5/8" to 1-7/8" Rod, 1-1/2" Pipe, DURIUM #6 (U-Bolt), Hex Nuts & SPLW

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	268
UPC	781810260296
UPC 12 Digit	7818102602966

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height fraction	4 in
Dimension - Height inch	4.00 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4
Conductor - Copper Solid Size Range	8-4
Conductor - Copper Str Size	8;7;6;5;4
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Str Size Range	8-4
Conductor - Copper Tube Std Size	1-5/8;1-3/4;1-7/8
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8
Conductor - Rod Size	1 5/8 in;1 3/4 in;1 7/8 in
Conductor - Rod Size Range	1 5/8 in-1 7/8 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)