



GD204C

by Burndy
Catalog ID: GD204C

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 3" Rod, 3" to 3-1/2" Pipe

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	258
UPC	781810238905
UPC 12 Digit	7818102389055

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.63 in
Dimension - Width fraction	4-7/8 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4
Conductor - Copper Solid Size Range	8-4
Conductor - Copper Str Size	8;7;6;5;4
Conductor - Copper Str Size B Range	3
Conductor - Copper Str Size Range	8-4
Conductor - Copper Tube Std Size	3
Conductor - Copper Tube Std Size Range	3
Conductor - Rod Size	3 in
Conductor - Rod Size Range	3 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)