



## GD2226

by Burndy  
Catalog ID: GD2226

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 4" to 4-1/2" Rod, 4" Pipe.

Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Tube (ips) Size: 4 IN, Ground Rod Size: 4 - 4-1/2 IN, Installation Torque: 240 IN-LB, Height: 6-3/8 IN, Width: 5-7/8 IN

## Product Details

### General

|                                       |   |
|---------------------------------------|---|
| Application                           | For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete |
| Installation Torque Recommended in-lb | 240 LBS/in  |
| Material                              | Copper Alloy, Cast  |
| Material Type - Screw                 | DURIMUM™ Silicon Bronze   |
| Plated                                | N   |
| Plating Type                          | Unplated  |
| Sub Brand                             | MECHANICAL CONNECTOR  |
| Type                                  | GD  |
| U Bolt Type                           | 261   |
| UPC                                   | 781810260463  |
| UPC 12 Digit                          | 7818102604633   |

### Dimensions

|                             |          |
|-----------------------------|----------|
| Dimension - B Length inch   | 1.63 in  |
| Dimension - Height fraction | 6-3/8 in |
| Dimension - Height inch     | 6.38 in  |
| Dimension - Width fraction  | 5-7/8 in |
| Dimension - Width inch      | 5.81 in  |
| Dimension - Width mm        | 148 mm   |

### Conductor Related

|                                     |                 |
|-------------------------------------|-----------------|
| Conductor - Copper Solid Size       | 4;3;2;1;1/0;2/0 |
| Conductor - Copper Solid Size Range | 4-2/0           |
| Conductor - Copper Str Size         | 4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Size B Range | 4               |
| Conductor - Copper Str Size Range   | 4-2/0           |
| Conductor - Copper Tube Std Size    | 4               |

|  |                          |
|--|--------------------------|
| Conductor - Copper Tube Std Size Range | 4                        |
| Conductor Size                         | #4 Sol AWG - 2/0 Str AWG |

### Certifications and Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)