



GG151

by Burndy
Catalog ID: GG151

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 1" IPS

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	244
UPC	781810260043
UPC 12 Digit	7818102600433

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height fraction	3-3/8 in
Dimension - Height inch	3.38 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Conductor Related

Conductor - Copper Tube Std Size	1 IPS IPS
Conductor - Rod Size	1 1/8 in;1 1/4 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	16
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)