



## GG161SE

by Burndy  
Catalog ID: GG161SE

RUN: IPS: 1 1/4" ROD: 1 3/8" - 1 1/2"

## Product Details

### General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	204
UPC	621945496804
UPC 12 Digit	0

### Dimensions

Dimension - B Length inch	1.38 in
Dimension - Braid Width Max fraction	1 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Height inch	3.50 in
Dimension - Width fraction	3 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

### Conductor Related

Conductor - Copper Str Size B Range	1.25
Conductor - Copper Tube Std Size	1-1/2
Conductor - Copper Tube Std Size Range	1-1/2
Conductor Type	<ul style="list-style-type: none"> <li>Rod-Size</li> <li>CU Tube Std-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)