



## GG171W

by Burndy  
Catalog ID: GG171W

Prop 65 Notice

ACCOM: 1-1/2 I.P.S. - 1-5/8-17/8 CU ROD

## Product Details

### General

|                                       |                        |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in             |
| Material                              | Copper Alloy           |
| Material Type - Screw                 | DURIUM™ Silicon Bronze |
| Plated                                | Y                      |
| Plating Type                          | Tin - Hot Dipped       |
| U Bolt Type                           | 199                    |
| UPC                                   | 781810207468           |
| UPC 12 Digit                          | 7818102074688          |

### Dimensions

|                                      |          |
|--------------------------------------|----------|
| Dimension - B Length inch            | 1.38 in  |
| Dimension - Braid Width Max fraction | 1 in     |
| Dimension - Braid Width Max inch     | 1.00 in  |
| Dimension - Height inch              | 3.50 in  |
| Dimension - Width fraction           | 3-1/4 in |
| Dimension - Width inch               | 3.25 in  |
| Dimension - Width mm                 | 83 mm    |

### Conductor Related

|  |  |
|--|--|
| Conductor - Copper Str Size B Range    | 1.5  |
| Conductor - Copper Tube Std Size       | 1-5/8;1-3/4;1-7/8  |
| Conductor - Copper Tube Std Size Range | 1-5/8-1-7/8  |
| Conductor Type                         | <ul style="list-style-type: none"> <li>Rod-Size</li> <li>CU Tube Std-Size</li> </ul> |

### Certifications and Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |

### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)