

GG192TN

by Burndy
Catalog ID: GG192TN

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2-1/2"-2 7/8" Pipe, 4.56 in Width. Tin Plated



Product Details

General

| | |
|--------------|--------------------------------|
| Material | Copper Alloy, Cast, Tin Plated |
| Plated | Y |
| Plating Type | Tin Plated |
| U Bolt Type | 232 |
| UPC | 621945455771 |
| UPC 12 Digit | 6219454557711 |

Dimensions

| | |
|---------------------------|---------|
| Dimension - B Length inch | 1.75 in |
| Dimension - Width inch | 4.56 in |
| Dimension - Width mm | 116 mm |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - UL Listed Direct Burial | Yes |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)