



GG2025

by Burndy
Catalog ID: GG2025

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 3"-3-1/2" Pipe,

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	282
UPC	781810260104
UPC 12 Digit	7818102601044

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Width fraction	5-1/4 in
Dimension - Width inch	5.19 in
Dimension - Width mm	132 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)