



# GG203

by Burndy  
Catalog ID: GG203

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 3"-3-1/2" Pipe,Torque: 480 lb-in

## Product Details

### General

|                                       |                        |
|---------------------------------------|------------------------|
| Installation Torque Recommended in-lb | 480 LBS/in             |
| Material                              | Copper Alloy, Cast     |
| Material Type - Screw                 | DURIUM™ Silicon Bronze |
| Plated                                | N                      |
| Plating Type                          | Unplated               |
| U Bolt Type                           | 282                    |
| UPC                                   | 781810260111           |
| UPC 12 Digit                          | 7818102601111          |

### Dimensions

|                            |          |
|----------------------------|----------|
| Dimension - B Length inch  | 2.00 in  |
| Dimension - Width fraction | 5-1/4 in |
| Dimension - Width inch     | 5.19 in  |
| Dimension - Width mm       | 132 mm   |

### Certifications and Compliance

|                                         |       |
|-----------------------------------------|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | No    |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 2 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)