



GG222

by Burndy
Catalog ID: GG222

Prop 65 Notice

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 4" Pipe, 4"-4-1/2" Rod, 6.19 W.

Features: High Copper Alloy Ground Connector For Joining Bar, Strap, Braid Or Cable To Rod Or Tube, High Copper Alloy Cast Body, DURIUM U-Bolts, Nuts And Lockwashers Make The GG Particularly Effective For Use With Braid For Ground Rods, Switch Handles, Fence Posts And Gates, One-Wrench Installation, Dimension A: 2 IN, Ground Rod Size: 4 - 4-1/2 IN, Tube (ips) Size: 4 IN, Installation Torque: 480 IN-LB, Width: 6-1/4 IN, Height: 6-1/2 IN

Product Details

General

Application	For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GG
U Bolt Type	236
UPC	781810990070
UPC 12 Digit	7818109900700

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Width inch	6.19 in
Dimension - Width mm	157 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)