

GIE2CG3

by Burndy
Catalog ID: GIE2CG3

Prop 65 Notice

Mechanical Grounding Connector, For Flexible Rubber Sheath Cable, 6 AWG - 2 AWG.

Features: Accommodates Flexible Rubber Sheath Cable Ranging From #6 To #2 Conductor, Length: 4.62 IN, Width: 36 IN, Height: 1.94 IN



Product Details

General

Application	For Used To Accommodates Flexible Rubber Sheath Cable Ranging From #6 - #2 Conductors
Material	Copper Alloy, Cast
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GIE-G
UPC	781810052297
UPC 12 Digit	7818100522977

Dimensions

Dimension - Length Overall inch	4.31 in
Dimension - Width inch	3.06 in
Dimension - Width mm	78 mm

Conductor Related

Conductor Size	#6 AWG - #2 AWG
----------------	-----------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)