



# GK1526

by Burndy  
Catalog ID: GK1526

Prop 65 Notice

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 1" Pipe, 1-1/8" - 1-1/4" Rod, 3/8" Stud

## Product Details

### General

|                                       |                             |
|---------------------------------------|-----------------------------|
| Installation Torque Recommended in-lb | 240 LBS/in                  |
| Material                              | Copper Alloy, Cast          |
| Material Type - Screw                 | DURIUM™ Silicon Bronze      |
| Plated                                | N                           |
| Plating Type                          | Unplated                    |
| Type                                  | Three Cables to Rod or Tube |
| UPC                                   | 781810233702                |
| UPC 12 Digit                          | 7818102337022               |

### Dimensions

|                            |          |
|----------------------------|----------|
| Bolt Size                  | 3/8 in   |
| Dimension - B Length inch  | 1.50 in  |
| Dimension - Height inch    | 3.31 in  |
| Dimension - Width fraction | 3-1/2 in |
| Dimension - Width inch     | 3.50 in  |
| Dimension - Width mm       | 89 mm    |

### Conductor Related

|                            |                          |
|----------------------------|--------------------------|
| Conductor - Rod Size       | 1 1/4 in                 |
| Conductor - Rod Size Range | 1 1/4 in                 |
| Conductor Size             | #4 AWG Sol - 2/0 AWG Str |

### Certifications and Compliance

|                                         |       |
|-----------------------------------------|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | Yes   |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 8 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)