



GK6434

by Burndy
Catalog ID: GK6434

Prop 65 Notice

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 300 kcmil - 500 kcmil, 3/8" Pipe, 5/8" - 3/4" Rod, 1/2" Stud.

Features: High Copper Alloy Ground Connector For Joining Three Equal Cables To Rod Or Tube, Cable Grooves Take A Wide Range Of Cable, High Copper Alloy Cast Body And DURIMUM U-Bolts, Nuts, And Lockwashers Make The GK Suitable For Direct Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Ground Rod Size: 5/8 - 3/4 IN, Tube (ips) Size: 3/8 IN, Installation Torque: 480 IN-LB, Width: 4 IN, Height: 3-1/2 IN

Product Details

General

Application	For Joining Three Equal Copper Cables To Rod Or Tube, Direct Burial In Earth Or Concrete
Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	Three Cables to Rod or Tube
UPC	781810233542
UPC 12 Digit	7818102335422

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.75 in
Dimension - Height inch	3.44 in
Dimension - Width inch	4.00 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - Rod Size	5/8 in ; 3/4 in
Conductor Size	300 kcmil - 500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)