



GKA8C

by Burndy
Catalog ID: GKA8C

Prop 65 Notice

Cu Direct Burial Ground Terminal, #10 AWG Sol-#8 AWG Str, #10 Hole Size, Stainless Steel H/W

Product Details

General

Installation Torque Recommended in-lb	25 LBS/in
Material	Copper Alloy
Material Type - Screw	Steel - Stainless
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
UPC	781810100981
UPC 12 Digit	7818101009811

Dimensions

Dimension - B Length inch	0.31 in
Dimension - Height inch	0.58 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG
Conductor - Copper Solid Size Range	10 AWG-7 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Size Range	10 AWG-8 AWG
Conductor Type	- CU C Str-Size - CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)